




注記
NOTES


- 材質
ハウジング：耐熱性ナイロンUL94V-0
ピン：銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール：銅合金、ニッケル下地、錫メッキ
MATERIAL
HOUSING:POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FITTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 色：ナチュラル、黒、赤、青
COLOR:NATURAL, BLACK, RED, BLUE
- 嵌合相手
ハウジング：502351-**0*
錫メッキ端子：50212-8*00,50372-8*00,560085-0101
金メッキ端子：56161-8*81
MATES WITH
HOUSING:502351-**0*
SN PLATING TERMINAL:50212-8*00,50372-8*00,560085-0101
AU PLATING TERMINAL:56161-8*81
- エンボス梱包品の詳細はSD-502352-002参照
DETAILED TAPING PACKAGE, SEE SD-502352-002.
- ELV及びRoHS適合
ELV AND RoHS COMPLIANT
- 半田付け面のコプラナリティ：0.1mm MAX.
CO-PLANARITY OF SOLDERING TAILS TO BE 0.1mm MAX.

7.一般公差
GENERAL TOLERANCES
10 UNDER: ±0.2
10 OVER 30 UNDER: ±0.25
30 OVER: ±0.3
ANGULAR: ±3°

INITIAL REVISION:
DRWN SHSHIBATA 2007/12/18
CHECK HKOMATSU 2007/12/18
APPR AKANESHIGE 2007/12/18

FUNCTIONAL SYMBOLS A = 0 B = 0 C = 0 D = 0 E = 0 F = 0 G = 0 H = 0 I = 0 J = 0 K = 0 L = 0 M = 0 N = 0 O = 0 P = 0 Q = 0 R = 0 S = 0 T = 0 U = 0 V = 0 W = 0 X = 0 Y = 0 Z = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
	DIMENSION UNITS	SCALE
	mm	5:1
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL	± 0.5°	
4 PLACES	±	
3 PLACES	±	
2 PLACES	±	
1 PLACE	±	
0 PLACES	±	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		
THIRD ANGLE PROJECTION		
DRAWING		
A3-SIZE		
SERIES		
502352		
MATERIAL NUMBER		
SEE CHART		
CUSTOMER		
GENERAL MARKET		
SHEET NUMBER		
1 OF 4		

CURRENT REV DESC: For fixing wrong view of 6ckt			
STATUS: Production			
DRWN: Hideo Yoneyama			
CHK'D: Hiromichi Komatsu			
APPR: Takashi Iida			
2024-05-14			
2024-05-16			
2024-05-16			
DOCUMENT NUMBER			
SD-502352-001			
DOC TYPE			
PSD			
DOC PART			
001			
REVISION			
L4			
PRODUCT SALES DRAWING			
2.0MM PITCH W/B CONN. WAFFER ASSY R/A SMT			
molex			



注記
NOTES

1. 製品番号

ナチュラル・錫めっき: 502352-**00

ナチュラル・金めっき: 502352-**10

黒・錫めっき: 502352-**01

赤・錫めっき: 502352-**02

青・錫めっき: 502352-**03

詳細寸法については、製品単体図面を参照下さい。

PART NO.

NATURAL Sn Plating: 502352-**00

NATURAL Au Plating: 502352-**10

BLACK Sn Plating: 502352-**01

RED Sn Plating: 502352-**02

BLUE Sn Plating: 502352-**03

SEE SALES DRAWING FOR CONNECTOR

2. 梱包数量: 700個/リール

NUMBER OF CONNECTORS 700PCS/REEL

3. リードテープ長さ

LEAD TAPE LENGHT

4. 材料

MATERIAL

キャリアテープ: ポリスチレン

CARRIER TAPE: POLYSTYRENE

トップテープ: PET, PE, PEF

TOP TAPE: PET, PE, PEF

リール: ポリスチレン

REEL: POLYSTYRENE

5. 一般公差


GENERAL TOLERANCES

10 UNDER: ± 0.2

10 OVER 30 UNDER: ± 0.25

30 OVER: ± 0.3

ANGULAR: $\pm 1^\circ$



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:					
mm		NTS						molex	
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL		±	°						
4 PLACES		±							
3 PLACES		±							
2 PLACES		±							
1 PLACE		±							
0 PLACES		±							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		502352	

