RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN

Specifications(规格)：
1.Impedance(特性阻抗)：50Ω;
2.Frequency（工作频率）：DC～6GHz;
3.VSWR （电压驻波比）：1.60 Max.
4.Insulation resistance(绝缘阻抗)：≥100MΩ;
5.Dielectric withstand voltage（介质耐电压）：800V AC;
6.Mating cycles（耐久性）：≥25 cycles;
7.Retention force latch(保持力)：≥110N;
8.Temperature range(使用温度)：-40℃～+105℃;

PART NO.:

X Z X R X - M2F-XXXX-K1M- X X
① ② ③ ④ ⑤


① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302/RTK031
8: RG174LL

② Successive number: 1~Z


③ Length (mm): 1000=1000mm

④ Coding A: A~Z

⑤ Coding B: A~Z



接 点 表(Wiring Table)



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ7RH-M2F-500-K1M-ZZ	500 [19.685]	±10 [0.394]
XZ7RH-M2F-1000-K1M-ZZ	1000 [39.370]	±15 [0.591]
XZ7RH-M2F-2000-K1M-ZZ	2000 [78.740]	±20 [0.787]
XZ7RH-M2F-3000-K1M-ZZ	3000 [118.110]	±30 [1.181]
XZ7RH-M2F-4000-K1M-ZZ	4000 [157.480]	±60 [2.362]

NO.	NAME	SPEC.	Q'TY	NOTE
3	Connector	FAKRA Male connector,Z Code	2SET	
2	Connector	Horizontal Double MINI FAKRA Female Connector,Z Code	1SET	R版
1	Cable	RTK031 Cable PVC OD3.30 Black,-40~105℃	2PCS	

XKB 星创 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希 文	VIEW:	MODEL TYPE: Assembly cable, Horizontal,Double MINI FAKRA series
CHECKED		UNIT: mm/in	PART NO.: XZ7RH-M2F-XXXX-K1M-ZZ
APPROVED		SIZE: A4	DWG NO.: X-XZ7RH-M2F-XXXX-K1M-ZZ

SCALE	PAGE	REVISION
N/A	1/1	A0