# 1-2308346-3 ✔ ACTIVE


Rail D-Sub Backshells


TE Internal #: 1-2308346-3

Shielded, Backshell, Steel, Straight, Shell Size 5, 50 / 78 Position, Crimp Ferrule Termination, Rail D-Sub Backshells

View on TE.com >

Connectors > Connector Accessories > Connector Backshells > D-SUB BACKSHELL SIZE 5







Connector Backshell Product Style: **Shielded**

Connector Backshell Product Type: **Backshell**

Primary Product Material: **Steel**

Body Orientation: **Straight**

Compatible With Connector Shell Size: **5**

All D-SUB BACKSHELL SIZE 5 (8)

## Features

### Industry Standards

| | |
|---|---|
| UL Flammability Rating | UL 94V-0 |

### Mechanical Attachment

| | |
|---|---|
| Mating Retention Type | Jackscrew |
| Thread Size | 4-40 UNC |

### Body Features

| | |
|---|---|
| Cable Exit Angle | 180°, 45° |
| Primary Product Material | Steel |

### Product Type Features

| | |
|---|---|
| Connector Backshell Product Style | Shielded |
| Connector Backshell Product Type | Backshell |
| Sealable | No |
| Termination Device Type | Crimp Ferrule |

### Housing Features

| | |
|---|---|
| Body Orientation | Straight |
| Compatible With Connector Shape | D-Shaped |

### Operation/Application

| | |
|---|---|
| Compatible With Connector Shell Size | 5 |

### Configuration Features

| | |
|---|---|
| Number of Positions | 78, 50 |

### Usage Conditions

| | |
|---|---|
| Operating Temperature Range | -40 – 90 °C[-40 – 194 °F] |

### Other

| | |
|---|---|
| EU RoHS Compliance | Compliant with Exemptions |

## Product Compliance

For compliance documentation, visit the product page on TE.com>


| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Not Yet Reviewed |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JAN 2024 (240)<br>SVHC > Threshold:<br>Pb (3.5% in Component Part)<br>**Article Safe Usage Statements:**<br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## Compatible Parts



TE Part # 1-2308348-8
CRIMP FLANGE 8 LARGE


## Also in the Series | Rail D-Sub Backshells



Connector Backshells(55)



Connector Contacts(5)



Connector Hardware(19)



Connector Strain Relief(67)



Crimp D-Sub Connectors(10)



Insertion & Extraction Tools(2)


## Customers Also Bought




TE Part #CAT-R131-C1121A
Cable Clamp for Size 4-5 STD/5QL Shell



TE Part #2-111196-2
60 RCPT SYSTEM 50, LEAD FREE



TE Part #1879217-7
CPF 0603 240K 0.1% 25PPM 1K RL




TE Part #1-2176088-1
RP 1J 0.166W 953R 0.1% 25PPM 1K RL



TE Part #6-1879133-1
RN 0603 3K74 0.1% 10PPM 1K RL



TE Part #6-2176216-0
CPF A 0603 91K 0.1% 25PPM 1K RL



TE Part #2176313-2
RP 1E 0.1W 137K 0.1% 25PPM 1K RL



TE Part #7574444009
RAYRIM-NR8-0-SP

TE Part #839220-E
IDCCS SRC 1,27 4 * SPX SPX 150 PVC

## Documents

### Product Drawings

FULL METAL HOODS SIZE 5 - 3 (RAW)

English

### CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2308346-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2308346-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2308346-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

### Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English