



RECOMMENDED PCB LAYOUT  
TOP VIEW (. XX ± 0.05)

规格料号	DIM A	DIM B	DIM C
HYCW-BB4P5080D-C150	8.00	5.70±0.3	6.85±0.3
HYCW-BB4P5092D-C150	9.25	6.95±0.3	8.10±0.3
HYCW-BB4P50105D-C150	10.50	8.20±0.3	9.35±0.3

性能:

- 额定电流: 3.0A
- 额定电压: 12V
- 耐电压: 500V
- 接触电阻: 30mΩ MAX
- 绝缘电阻: 500MΩ
- 工作温度: -40℃ ~ +85℃
- 塑件(材质): LCP黑色
- 接触点(材质): 铜合金, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY:	DATE:	PART NAME:	
	陈一鸣	2014-02-23	5.0PH 4P 侧压电池座 有柱 插件脚	
	CHECKED BY:	DATE:	PART NO.	SEE TABLE
	马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE:	DRAW NO:	HYC-2604141559
	邱敏	2014-02-23	SHEET NO.	1 OF 1