

SIGN	DATE	DESCRIPTION	APPROVER
1			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!







Material:

- Item Ⓐ Terminal housing: PBT (UL94V-0)
- Item Ⓑ Male contact : Copper. Gold plated.
- Item Ⓒ With flange nut: Steel zinc plated.

Electrical:	cULus
Voltage rating:	600 V
Current rating:	115 A
Withstanding Voltage:	2.2 KV
Operating temperature:	-40°C to +115°C
Soldering temperature:	250°C±10°C/5 Sec





KU xx C 0 x 0 xxxx G

- No. OF POLES
  - 02: 2 POLES
  - :
  - :
  - 10: 10 POLES
- COLOR
  - 0: BLACK
  - 5: GREEN (RAL 6018/T)
  - 6: BLUE
  - 8: GREY (RAL 7035/D)
- G: Pb<40000ppm
- 0000: "@" Logo (Standard)
- 000A: "ANYTEK" Mark
- Any special item by customer requst, please contact sales department.

POLE		2	3	4	5	6	7	8	9	10
Dim.L		31.4	46.4	61.4	76.4	91.4	106.4	121.4	136.4	151.4
Dim.P		15.0	30.0	45.0	60.0	75.0	90.0	105.0	120.0	135.0
Tol.		±0.20			±0.35			±0.50		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KU 15.0mm Body Series (Vertical) without flange 2P-10P				
PART NO.	KUxxC0x0xxxxG			DWG NO.	8KU0006
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2011.04.25	Runner 2010.05.24	UNIT: mm / SCALE: NONE / SHEET: 01/01 / REV.: B	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°