



REV.	DESCRIPTION	ECN NO.	NAME	DATE

**SPECIFICATIONS**  
 Current Rating: 1.0 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40° to +105°  
 Insulator Material: Polyester (UL94V-0)  
 Contact Material: Phosphor bronze  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
PM-1.27-2*01-4.3-SM	2*1	0.00	1.27
PM-1.27-2*02-4.3-SM	2*2	1.27	2.54
PM-1.27-2*03-4.3-SM	2*3	2.54	3.81
PM-1.27-2*04-4.3-SM	2*4	3.81	5.08
PM-1.27-2*05-4.3-SM	2*5	5.08	6.35
PM-1.27-2*06-4.3-SM	2*6	6.35	7.62
PM-1.27-2*07-4.3-SM	2*7	7.62	8.89
PM-1.27-2*08-4.3-SM	2*8	8.89	10.16
PM-1.27-2*09-4.3-SM	2*9	10.16	11.43
.....	.....	.....	.....
PM-1.27-2*50-4.3-SM	2*50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x° ±5' x.x° ±1' x.xx° ±0.5'	TITLE: 1.27FH H4.3 2xNPin SMT				
	U型 PC4.8 PB4.6 6T				
	DWG. NO.: PM-1.27-2*N-4.3-SM	CHECKED: MAX			
PART NO.: PM-1.27-2*N-4.3-SM		DRAWN: ELLA		APPROVED: WILL	
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4		