









REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术要求Specification:

1. 材质 Material: PA66 UL94V-0;
2. 额定电流 Current rating: 3.0A AC, DC
3. 额定电压 Voltage rating: 250V AC, DC
4. 温度范围 Temperature range: -25℃ to +85℃
5. 接触电阻 Contact resistance: ≤20mΩ
6. 绝缘电阻 Insulation resistance: ≥1000MΩ
7. 耐压 Withstand voltage: 1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C	D
CXH-2Y-JK	2	2.50	5.70	3.70	3.70
CXH-3Y-JK	3	5.00	8.20	6.20	6.20
CXH-4Y-JK	4	7.50	10.70	8.70	8.70
CXH-5Y-JK	5	10.00	13.20	11.20	11.20
CXH-6Y-JK	6	12.50	15.70	13.70	13.70
CXH-7Y-JK	7	15.00	18.20	16.20	16.20
CXH-8Y-JK	8	17.50	20.70	18.70	18.70
CXH-9Y-JK	9	20.00	23.20	21.20	21.20
CXH-10Y-JK	10	22.50	25.70	23.70	23.70
CXH-11Y-JK	11	25.50	28.20	26.20	26.20
CXH-12Y-JK	12	27.50	30.70	28.70	28.70
CXH-13Y-JK	13	30.00	33.20	31.20	31.20
CXH-14Y-JK	14	32.50	35.70	33.70	33.70
CXH-15Y-JK	15	35.50	38.20	36.20	36.20
CXH-16Y-JK	16	37.50	40.70	38.70	38.70

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±1*	PART NO.		TITLE:	
.XX ±0.20		CXH-XY-JK		XH2.5MM HOUSING	
.XXX ±0.10		DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		SCALE SHEET N:A 1/1	
MATERILA	---	APPD: Ava			
FINISH	---				