



一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻:  $\leq 20m\Omega$
- 1-3. 绝缘电阻:  $\geq 1000M\Omega$
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度:  $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度:  $+220^{\circ}C$ , 10s max

三. 材质:

- 3-1. 塑胶: PBT(Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

| PIN | A      | B     |
|-----|--------|-------|
| 1   | 2.54   | 0.00  |
| 2   | 5.08   | 2.54  |
| 3   | 7.62   | 5.08  |
| 4   | 10.16  | 7.62  |
| 5   | 12.70  | 10.16 |
| 6   | 15.24  | 12.70 |
| 7   | 17.78  | 15.24 |
| 8   | 20.32  | 17.78 |
| 9   | 22.86  | 20.32 |
| 10  | 25.40  | 22.86 |
| 11  | 27.94  | 25.40 |
| 12  | 30.48  | 27.94 |
| 13  | 33.02  | 30.48 |
| 14  | 35.56  | 33.02 |
| 15  | 38.10  | 35.56 |
| 16  | 40.64  | 38.10 |
| 17  | 43.18  | 40.64 |
| 18  | 45.72  | 43.18 |
| 19  | 48.26  | 45.72 |
| 20  | 50.80  | 48.26 |
| 21  | 53.34  | 50.80 |
| 22  | 55.88  | 53.34 |
| 23  | 58.42  | 55.88 |
| 24  | 60.96  | 58.42 |
| 25  | 63.50  | 60.96 |
| 26  | 66.04  | 63.50 |
| 27  | 68.58  | 66.04 |
| 28  | 71.12  | 68.58 |
| 29  | 73.66  | 71.12 |
| 30  | 76.20  | 73.66 |
| 31  | 78.74  | 76.20 |
| 32  | 81.28  | 78.74 |
| 33  | 83.82  | 81.28 |
| 34  | 86.36  | 83.82 |
| 35  | 88.90  | 86.36 |
| 36  | 91.44  | 88.90 |
| 37  | 93.98  | 91.44 |
| 38  | 96.52  | 93.98 |
| 39  | 99.06  | 96.52 |
| 40  | 101.60 | 99.06 |

浙江博穆精密电子有限公司

图名:

PC104-2\*NA+1

图号:

XXXXXXXXXXXXXXXXXXXX

未标注公差

|     |            |       |                 |
|-----|------------|-------|-----------------|
| XX. | $\pm 0.40$ | XX.°  | $\pm 2^{\circ}$ |
| X.  | $\pm 0.30$ | .XX.° | $\pm 1^{\circ}$ |
| .X  | $\pm 0.20$ |       |                 |
| .XX | $\pm 0.15$ |       |                 |

绘制:

韩金锋

单位:

MM

签发:

比例:

1:1

审核:

视图:

