

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

- 4mm BANANA PLUG LEAD, STACKING SHEATHED PLUG TO STACKING SHEATHED PLUG, 0.75mm², SILICONE JACKETED WIRE. CE MARK AND CSA LISTED (US AND CANADA).
- SPECIFICATIONS:
 WIRE:
 REINFORCED SILICONE (-60° C TO +180° C)
 195x0.07mm STRANDED BARE COPPER, 0.75mm² CROSS SECTION, 18 AWG, Ø.146±.008 (Ø3.7±0.2mm) O.D.

 INSULATED HOUSING:
 POLYPROPYLENE THERMOPLASTIC, UL94V-0.


 CONTACT:
 4mm, 9 LEAF, BERYLLIUM COPPER, NICKEL PLATED.
 PLUG BODY:
 BRASS, NICKEL PLATED.
- RATING:
 IEC 61010-031 1,000 V CAT III / 600 V CAT IV P2.
 CURRENT: 12 A MAX.
 TEMPERATURE: -25° C TO +80° C.

CE DECLARATION OF CONFORMITY, LVD
 CONFORMS TO RoHS DIRECTIVE 2011/65/EU
 EXEMPTION: ANNEX III, 6(c) - COPPER ALLOY CONTAINS UP TO 4% LEAD BY WEIGHT.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/12/99	
A	NOTE 3: ADDED IEC 61010-031 600 CAT IV & RoHS; REVISED PLUG CONFIGURATION, PAGE 2.	2/7/05	
B	REVISED NOTES 3.	5/18/11	


MODEL NUMBER

CT2521-L-#



THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610 TITLE TEST LEAD, 4 mm STACKING SHEATH BANANA PLUG TO STACKING SHEATH BANANA PLUG, 18 AWG (0.75mm²), SILICONE JACKET			
			APPROVALS	DATE				
MATERIAL		DRAWN	WDH	7/12/99	A	43F45	P252100	B
FINISH		CHECKED			SCALE		NONE	SHEET
NEXT ASSY		ENGR.					1 OF 2	
USED ON		DESIGN ACTIVITY						
APPLICATION								

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.



DRAWN		7/12/99		SIZE	CAGE CODE	DWG. NO.	REV.
WDH				A	43F45	P252100	B
CHECKED				SCALE	1:1	SHEET	2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2521-50-0](#) [CT2521-50-2](#) [CT2521-25-2](#) [CT2521-150-0](#) [CT2521-150-2](#) [CT2521-200-0](#) [CT2521-200-2](#) [CT2521-25-0](#) [CT2521-100-6](#) [CT2521-200-4](#) [CT2521-25-9](#) [CT2521-200-6](#) [CT2521-200-9](#) [CT2521-25-6](#) [CT2521-200-5](#) [CT2521-50-9](#) [CT2521-50-4](#) [CT2521-50-5](#) [CT2521-50-6](#) [CT2521-10-0](#) [CT2521-10-2](#) [CT2521-10-4](#) [CT2521-10-5](#) [CT2521-10-6](#) [CT2521-10-9](#) [CT2521-100-4](#) [CT2521-100-5](#) [CT2521-100-9](#) [CT2521-150-4](#) [CT2521-150-5](#) [CT2521-150-6](#) [CT2521-150-9](#) [CT2521-25-4](#) [CT2521-25-5](#) [CT2521-30-4](#) [CT2521-30-5](#) [CT2521-30-9](#) [CT2521-61-0](#) [CT2521-61-2](#) [CT2521-91-6](#) [CT2521-183-2 Red](#) [CT2521-183-5 Green](#) [CT2521-92-0 Black](#) [CT2521-92-2 Red](#) [CT2521-92-9 White](#)