


GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1
Ⓒ	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15

	PART NO. AND CH. CODE	COLOR
1	7183-2510,A (7B83-2510,A)	NATURAL
	7183-2510-30,A	BLACK
2	7183-2510-40,A	LIGHT GRAY
2	7183-2510-50,A	ORANGE
2	7183-2510-60,A	GREEN
3	7183-2510-80,A	BROWN
2	7183-2510-90,A	BLUE







注記

1. 材質 : PBT
   色 : 色品番表参照
2. かん合相手品番 : 7282-1080 ETC.,7182-2410
3. 取扱説明書NO. YPES-15-408
1. ( )内品番は、エアバック(A／B)回路及び
   特別管理回路に使用する時に適用する事。

NOTES

1. MATERIAL : PBT
   COLOR : SEE TABLE
2. MATING PART NO. : 7282-1080 ETC.,7182-2410
3. HANDLING MANUAL NO. YPES-15-408
1. PART NUMBERS IN PARENTHESIS SHALL BE USED FOR
   AIR BAG(A/B) CIRCUITS AND OTHER CIRCUITS DESIGNATED
   FOR SPECIAL MONITORING.

ISSUE MARK

LET	DATE	REVISION RECORD	NO.	CHKD
3	10/12/08	CHANGED PART NAME,ETC.	C10-ZB28	K.K
2	06/02/02	ADDED COLOR PART NO.,ETC.	C06-Z104	E.S
1	04/02/02	ADDED A/B PART NO.	C04-X070	S.N
	03/08/06	NEW,A	C03-X492	E.F

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15

SPECIFIED

MASS

CUSTOMER				
CUSTOMER PART NO.		CUSTOMER DWG NO.		
OFFICE		TRIAL PART NO.		
VENDOR				
VENDOR NO.				

DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	03/08/06	mm	2:1	3

APPROVED	CHECKED	CHECKED	DESIGN	DRAWN
M.FUKUDA	O.SUGIYAMA	K.KIDA	E.FUKUDA	M.ALAGAR
10/12/08	10/12/08	10/12/08	02/09/11	10/12/08

MATL. SPEC.	SEE NOTES
TREAT. & FIN.	
NAME	3 HLC 2.3Ⅱ(090Ⅱ) 8P HOUSING FEMALE
PART NO. CH. CODE	1 7183-2510 ETC. (7B83-2510, A)
DWG NO.	7183-2510:R
SET DWG NO.	
	YAZAKI CORPORATION