

REV.	DESCRIPTION	ECN NO.	NAME	DATE


规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.0A/contact terminal
2. 额定电压: Voltage Rating 30V DC
3. 接触电阻: Contact Resistance 50 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage: 300 V AC AT Sea Level
5. 绝缘电阻: Insulation Resistance:  
100MEGA ohms MIN

原材料: Raw material:

1. 塑胶: Plastic cement:  
High Temperature Thermoplastics,  
LCP Black
  2. 端子: Contact: Copper Alloy C2680/C5191
  3. 外壳: Shell: SPCC/Copper Alloy C2680
- 电镀: Electroplate:
1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Tails
  2. 外壳: Shell:  
Nickel Plating

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. x. x.x x.xx GENERAL ANGLE: x. x.x' x.xx'	TOL. ±0.30 ±0.20 ±0.10 ±5.0° ±2.0°	TITLE: MINI USB 5P/F SMT B型(0.3T, 0.6柱)		
UNIT: mm		DWG. NO.: MINI-USB-5P	CHECKED: MAX	
SCALE: none		PART NO.: MINI-USB-5P	DRAWN: ELLA	
SHEET: 1 of 1		DWG. SIZE: A4	LAYER: bxconn	
APPROVED: WILL				