








RoHS compliant



PCB hole pattern, mounting side





No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
5	2	Snap-in bolt	PCB 1.6mm / Brass	tin plated
4	4	High power contact	FMP016P105	40A
3	5	Signal contact	P1 / Brass	AuroPur
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	green

Measurement without tolerance acc. to ISO 2768-m

SCALE 2:1

TITLE: D-Sub Mixed-Layout Connector

DRAWN: NAME / DATE tschneider01 18-04-2017

CHECKED: MTeubel 18-04-2017

FCT a molex company

DWG.NO. FM9W4P1A-1328

REV. 1

REV. | DATE | CH.-NO. | ORIGINAL: DIN A3-DRAWING AS A FILE

REPLACEMENT FOR:

PAGES 1

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING, WITHOUT OUR PRIOR CONSENT, IT MAY NOT BE COPIED, PASSED ON OR MADE AVAILABLE TO A THIRD PARTY AND IT MAY NOT BE USED FOR ANY PURPOSE NOT EXPRESSLY AUTHORISED BY US. AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.