

# Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u", 表面镀镀金1.5U

Contact: Bronze, 1.5U" GOLD PLATING OVER ALL  
30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.


温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C

# Ordering Information

F136-12 02 A2 B MU B2

NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL:	PACKING
2-40P	Full of Gold	B: PA6T	A: PE Bag
	Semi-gold	C: PA6T	B: Tape & Reel
		D: LCP	C: Tube
			D: Tube+CAP
			E: Tray



RoHS  
COMPLIANT

客编: K9938

注意  
事项

- 带序号为必检尺寸
- 带\*为重点检验尺寸
- 保持力0.5kg Min (公司标准)

			OPERATION	SCALE	Fit	Yxcon 东莞市宇熙精密连接器有限公司			
			X.X ±0.25	UNIT	MM	Dongguan Yuxi Electronic Co., Ltd.			
			X.XX ±0.20	SIZE	A4	DESIGN	伍思远2023.11.21	PART NO.	F136-1202A2BMUB2
A0	2023.11.21	/	X.XXX ±0.10	SHEET	1/1	CHECK		TITLE:	PH2.54*3.6 2*2P SMT:7.2 总长5.08 (GRS)
REV	DATE	SYMBOL	Angle ±3°	PROJ.	APPROVE			Cust order No.	U型 带柱 镀金1.5U 青铜 PA6T CAP+卷装/850PCS
			DIM TOL						

新版发行

MODIFICATION DESCRIPTION