



Technical Index:

1. Temperature range:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 5A AC, DC.
4. Contact resistance:  $\leq 20\text{m}\Omega$ .
5. Dielectric withstanding voltage: 1500V AC/minute.
6. Insulation resistance:  $\geq 1000\text{M}\Omega$ .
7. Apply to gauge: AWG#22~#28 (O.D 1.80mm Max).

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE
			.X±0.30	X.°±5°	审核 CHECK	LEO
			.XX±0.25	X.X°±5°	核准 APPROVAL	JOHN
			.XXX±0.15		单位 UNITS	MM
					比例 SCALE	1:1

料号 PART NO.	ZX-5557-4.2-2-DZ	版本 REV.	A
品名 TITLE	WBM4.2MM TERMINAL	页次 SHEET	1/1
客户料号 CUTM.NO.			
 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			