


WWW.XYECONN.COM

REV.	Q'TY	ECN. NO.	APR.	DATE










[Schematic]



[P.C.B.LAYOUT]

NOTES:

1.Specification:

1>.Operation force: 1000gf Max.
2>.Operation Temperature: -30℃ to +85℃.
3>.Storage Temperature: -40℃ to +85℃.
4>.Mechanical Life: 1000 cycles operations.
5>.Resistance to Soldering: 260±5℃ for 3-5 Seconds.

2.PLATING:

1>.GOLD flash 1u"(min) SOLDERTAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

1>.Non-switch Rating:100mA at 50V DC.
2>.Switching Rating: 25mA at 24V DC.
3>.Contact Resistance: Inital 50mΩ Max.
Contact Resistance: After life 100mΩ Max.
4>.Insulation Resistance:100MΩ Min at 100VDC.
5>.Dielectric Strength: 300V AC for 60seconds.
6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

XY-DSHP XX I S-R
(包装方式:T=Tub R=Reel)
(端脚型:S=贴片 / D=插件 / J型)
(L=高柄 / S=低柄 / T=低柄贴胶)
(开关位数: 02位-----10位)

5.PACKING: 2000pcs/Reel/Box.

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.°± 5°	APR. Alex	TITLE: PRODUCT Family DSHP Series Pitch 1.27mm	
.XX±0.25	.X°± 3°	CHK. Jack	DWG NO. XY-DSHP08TS-R	
.XXX±0.15	.XX°± 1°	DRA. Can	PROJ.	CUSTOMER DRAWING
			SIZE A4 / SCALE 1:1 / SHEET 1/1 / REV. A	

F-RD-18A