


A-A SECTION



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.0 Amps
 Withstanding Voltage: AC 500V
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Operation Temperature: -40° to +105°
 Insulator Material: Polyester (UL94V-0)
 Contact Material: Brass
 Standard: PA6T
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30-60 seconds
 (260° C for 5 seconds)

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
—	—	—	22	12.70	13.97	42	25.40	26.67
—	—	—	24	13.97	15.24	44	26.67	27.94
6	2.54	3.81	26	15.24	16.51	46	27.94	29.21
8	3.81	5.08	28	16.51	17.78	48	29.21	30.48
10	5.08	6.35	30	17.78	19.05	50	30.48	31.75
12	6.35	7.62	32	19.05	20.32	52	31.75	33.02
14	7.62	8.89	34	20.32	21.59	54	33.02	34.29
16	8.89	10.16	36	21.59	22.86	56	34.29	35.56
18	10.16	11.43	38	22.86	24.13	58	35.56	36.83
20	11.43	12.70	40	24.13	25.40	60	36.83	38.10



深圳市韩下电子有限公司


UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°
 X.X : ±0.25 X.X° : ±1°
 X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME: HX JN1.27-2x5P ZZ H4.9

SIZE	A4	SCALE	N:1	PROCT NO.
REV	A	UNIT	mm	PROJECT

DRAW: 黄彬 2023/11/09 CHECKED: 张伟 2023/11/09 APPROVED: 罗小春 2023/11/09



PAGE 1/1