









REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	/		更新外观图 更新图纸框	2025.01.15	桑 葚



Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-001-D2-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-001-D2-02	DC5V	20mA	20mA	1.9V	2.4V
Blue	TM-001-D2-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-001-D2-04	DC5V	20mA	20mA	1.7V	2.4V
Yellow	TM-001-D2-05	DC5V	20mA	20mA	1.7V	2.4V



序号	名称	材料	数量	镀层/颜色	备注
7	圆帽	PC	1	光油银白	借A0662右电盖
6	圆框	PA66	1	黑色	A0667
5	LED灯		1		借A0635红光
4	斜边按钮	PA66-G30	1	银白	A0667
3	弹片	不锈钢	1	Ag	借A0630
2	底座	PA66	1	黑色	借A0630
1	卡件	FR2	1	Ag	借A0630

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW:		MODEL TYPE:	LED SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TM-001-D2-X
APPROVED		SIZE:	A4	DWG NO.:	