

ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE




SPECIFICATION:
- Current Rating: 3AMP
- Temperature Range: -40℃to+105℃
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 1000MΩ Min
- Withstanding Voltage: AC 500V

Material:
- Insulator: Polyester (UL94V-0)
- Standard: PA6T
- Contact: Brass
- Plating: Au over Ni







COSTOMER DRAWING				深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING				TITLE	排针 PIN距2.0 塑高2.0 双排15PIN直插	REV.	A
CHECKED				PART NO.	LAIL-PZ2.0-15PX2-L	UNITS	mm
APPROVED				DWG. NO.		Projection	
TOLERANCES ARE							
30-150	±0.35	ANGLE					
10-30	±0.2						
5-10	±0.15	±3°					
0-5	±0.1						