





Dimension A&B


DIM A	N×5.0
DIM B	(N-1)×5.0

N=Number of contacts


Poles	A&B Tolerance
2P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



N=Number of contacts



P.C.B LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△	01/18/07	Soldering temperature changed from 245° to 250°	Tason
△	01/18/07	Part NO is Changed	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- △ Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: CE, RoHS

△ YM xx 01 x 0 xxxx G

04 2x2 CONTACTS
06 2x3 CONTACTS
... ..
48 2x24 CONTACTS

0 Black
5 Green
6 Blue
8 Grey

0000:"@Logo (Standard) Pb < 40,000ppm (RoHS)
000A:"ANYTEK"Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YM-5.0mm -L Series						
PART NO.		YMxx01x0xxxxG			DWG NO.		8YM0001	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			熊海燕 2007.01.25	熊海燕 2007.01.25		UNIT: mm	X. ±0.50	
						SCALE: NONE	X.X ±0.30	
						REV: D	X.XX ±0.10	
SHEET: 01/01					REV: D	X° ±1°		