

646478-5 ✓ ACTIVE

Z-PACK | Z-PACK 2mm HM


TE Internal #: 646478-5

PCB Mount Shroud, Gray, Glass Filled Polyester, 154 Position, Z-PACK 2mm HM

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **PCB Mount Shroud**

Primary Product Color: **Gray**

Primary Product Material: **Glass Filled Polyester**

Number of Positions: **154**

Operating Temperature (Max): **125 °C [ 257 °F ]**

## Features

### Product Type Features

Connector Cover Type	PCB Mount Shroud
----------------------	------------------

### Configuration Features

Number of Rows	7
Number of Positions	154

### Body Features

Primary Product Color	Gray
Primary Product Material	Glass Filled Polyester

### Mechanical Attachment

Mating Alignment Type	Guide Lugs
Mating Alignment	With

### Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

### Dimensions

Product Width	15.4 mm[.606 in]
---------------	------------------



Product Length	49.85 mm[1.96 in]
----------------	-------------------

Product Height	14.9 mm[.586 in]
----------------	------------------

Row-to-Row Spacing	2 mm[.079 in]
--------------------	---------------

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

### Operation/Application

Assembly Process Feature	Board Standoff
--------------------------	----------------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--






#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



## Compatible Parts



### Also in the Series | Z-PACK 2mm HM



### Customers Also Bought







TE Part #2007637-5  
SFP+ assy 2x2 Spring Fingers 4 LP Sn



TE Part #120953-1  
TE UPM Ver Receptacle 4P HC Power



TE Part #2176550-1  
RLW73P A3 1% R010 600ppm 4k RL



TE Part #PF0000313  
P061PT100C\_4.0X\_40 \_\_\_X 2N26S



TE Part #PF0001511  
P011PT500B\_8.0X\_70 \_\_\_\_ 2N



TE Part #PF0002215  
P011PT500B\_8.0X\_65 \_\_\_\_ 2N

## Documents

### Product Drawings

[2MM H.M., "A" SHROUD, 4.5MM](#)

English

### CAD Files

[3D PDF](#)

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_646478-5\\_F.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_646478-5\\_F.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_646478-5\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Application Specification](#)

English