



2.00±0.20 [0.079]



4.75±0.15 [0.187]

#4-40UNC

Specifications:

规格:

Material: Brass

材料: 黄铜

Plating: 50u"MIN ; 80u"MIN

电镀: 50u"镍 ; 80u"镍

广东星坤科技股份有限公司

Δx	日期
Δx	日期
Δx	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A
DWN	VIEW:
CHKD	UNIT: mm/in
APPD	SIZE: A4

MODEL TYPE:	D-USB 螺母
PART NO.:	XDBLM
DWG NO.:	X-XDBLM

WEIGHT	SHEET	REVISION
	1/1	A0