



SPECIFICATIONS

- 1、 Current Rating: 1A AC, DC
- 2、 Voltage Rating: 50V AC, DC
- 3、 Temperatuer Range: -25°C~+85°C
- 4、 Contact Resistance: 20mΩ Max
- 5、 Insulation Resistance: 100MΩ Min
- 6、 Withstanding Voltang: 500V AC/minute
- 7、 Material: PA66, UL94V-0

编 号	尺寸 (mm)	
	A	B
A1001-02Y	1.00	5.00
A1001-03Y	2.00	6.00
A1001-04Y	3.00	7.00
A1001-05Y	4.00	8.00
A1001-06Y	5.00	9.00
A1001-07Y	6.00	10.00
A1001-08Y	7.00	11.00
A1001-09Y	8.00	12.00
A1001-10Y	9.00	13.00
A1001-11Y	10.00	14.00
A1001-12Y	11.00	15.00
A1001-20Y	19.00	23.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 Mapping	黄彬		料号 PART NO.	HX SH1.0-6Y		版本 REV.	A				
			X.±0.25	X.*±2'		审核 Audit	张伟		品名 TITLE	压线端子胶壳		页次 SHEET	1/1			
			.X±0.20	.X'±1'			核准 Approved			罗小春			客户料号 CUTM. NO.			
			.XX±0.15	.XX'±0.5'						单位 Units				MM	比例 SCALE	1:1
.XXX±0.10	.XXX'±0.5'															