Eaton 16NHG000B-690

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 690V, 16A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	16NHG000B-690
UPC	051712188395
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	51 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	151.3333333 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

Powering Business Worldwide

□□□□

AMPERAGE RATING	16 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH000
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	690 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	2.5 W
CONNECTION	Blade end
CONSTRUCTION	NH000
CONSTRUCTION SIZE	NH000
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch 170H0236 EBF Vertical fuse rail EBV Vertical fuse switch-disconnectors EBH Size 000 Horizontal fuse switch-disconnectors
MATERIAL	Ceramic body
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	690 V
TYPE	Fuse
SPECIAL FEATURES	Live gripping lug
APPLICATION	• industrial • Utilities, Solar, Wind

□□

DECLARATIONS OF CONFORMITY	eaton-low-voltage-nh-fuse-declaration-of-conformity-uk251149en.pdf eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250957en.pdf

RATED SWITCHING CAPACITY AC	120 kA

□□□□:
□□□□:
□□□:
□□:

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2026 □□ □□□□□□□□

□□□□□□□□□□□□□□□□□□□□□□□□□□□□□□