

Specification Sheet

Part Number: 156-02586



Cable tie and weld stud mounting base are supplied pre-assembled for ease and speed of installation
Mount features a "soft-push" design - no tools required to fit the parts to the stud

M5/T5/M6/T6 Stud Mount Tie 7.95" L, 50lb Tensile, PA66HIRHS, Black, 100/pkg

Article Number 156-02586

Type T50R0SBS5-6U

Color Black (BK)

Quantity Per bag

Product Description Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description M5/T5/M6/T6 Stud Mount Tie 7.95" L, 50lb Tensile, PA66HIRHS, Black, 100/pkg

Global Part Name T50R0SBS5-6U-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50

Minimum Tensile Strength (Metric) 200

Length L (Imperial) 7.95

Length L (Metric) 202.0

Fixation Method Stud Mount

Identification Plate Position none

Tie Closure plastic pawl

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.16

Bundle Diameter Min (Metric) 4.0

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Height H (Imperial) 0.05

Height H (Metric) 1.2

Stud Diameter (Metric)	M6 M5
Stud Diameter (Imperial)	0.20
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS PA66HS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar,

electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)