





REV	ECN NO.	APPD
B	HS-19-0189	ZO

规格 Specifications

额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	500mΩ max.	
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.	
操作力 Operation force	炉前260±60gf	炉后280±60gf
寿命试验 Operating Life	50,000 cycles	
行程 Travels	0.13±0.08mm	



RECOMMENDED P.C.B. LAYOUT
安装尺寸图

LAND PATTERN PLAN
印刷电路板焊盘参考图

PRODUCT NO. : 1TS015A***-***A30 - **

- 轻触开关
- 3X2系列
- 外形:
- A=两脚
- B=两脚无按柄
- 触点颜色:
- 底座颜色:
- 贴膜颜色:
- 操作力度:
- 初始颜色
- 则不启用
- 手感:
- 0=常规(弹片)
- 1=大手感(弹片)
- 2=小手感(弹片)
- 3=特殊手感(弹片)
- 材质:
- 0=初始材质
- 1=新增材质
- 3=3个弹片
- 依次增加
- 产品高度(H):
- 060=0.60mm
- 065=0.65mm
- 070=0.70mm
- 其它:
- CT=编带(非编带,不启用)

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	KNOB	1	POLYAMIDE	BLACK
4	FILM	1	POLYAMIDE	WHITE
3	DOME	2	SUS301	Ag-PLATED
2	HOUSING	1	POLYAMIDE	BLACK
1	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED
NAME(INTENDED USE)	3X2 SERIES TACT SWITCHES			
PART NO.(INTENDED USE)	1TS015A-2600-0600A30			
TITLE:	PRODUCT DRAWING			
DWG NO.:	1TS015A-2600-0600A30-CT			
CHKD:	M.H.L: 7/22 2019			
DR:	Y.Y.Chen 7/22 2019			
SCALE	SHEET 1/1			
REV.	B			