


PCB REFERENCE DIAGRAM
TOLERANCE:±0.05

G-Switch Specification:
 1. Current rated: 1.5A AC/DC
 2. Voltage rating: 125V AC/DC
 3. Withstanding voltage: 1000V AC for 1 min
 4. Contact resistance: $40m\Omega$ max.
 5. Insulation resistance: $500M\Omega$ min
 6. Durability cycle: 750 Cycles
 7. Operating temperature range: $-40^{\circ}C \sim +85^{\circ}C$

1	SHELL	COPPER ALLOY	NI PLATED
2	HOUSING	LCP	BLACK UL 94V-0
3	TERMINALS	CS210	Au6u" PLATED ON CONTACT AREA Tin PLATED ON SOLDER AREA
NO.	PARTS	MATERIAL	REMARKS



SCALE: 1:1	UNIT: mm	SIZE: A4	UNIT: mm	Title: Horizontal RJ45 Conn Compatible With RJ11
Unless otherwise General tolerance:				Model Code: GT-RJ56B-8P8C-A
X	±0.40			DRAWN
Xx	±0.30			CHECKED
Xxx	±0.20			APPROVED
Angles	±3°			DATE
		Xia	Chen	Chen
				2025.04.10



REV: A0	SHEET: 1/1
---------	------------