










REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C
JXT-AFC05-HF4P-H20	4	1.50	2.52	5.54
JXT-AFC05-HF5P-H20	5	2.00	3.02	6.04
JXT-AFC05-HF6P-H20	6	2.50	3.52	6.54
JXT-AFC05-HF7P-H20	7	3.00	4.02	7.04
JXT-AFC05-HF8P-H20	8	3.50	4.52	7.54
JXT-AFC05-HF9P-H20	9	4.00	5.02	8.04
JXT-AFC05-HF10P-H20	10	4.50	5.52	8.54
JXT-AFC05-HF11P-H20	11	5.00	6.02	9.04
JXT-AFC05-HF12P-H20	12	5.50	6.52	9.54
.....				
JXT-AFC05-HF60P-H20	60	(60-1)*0.5	(60+8)*0.5+0.02	(60+7)*0.5+0.04
JXT-AFC05-HF80P-H20	80	(80-1)*0.5	(80+8)*0.5+0.02	(80+7)*0.5+0.04



序号	品名	材质
1	0.5后翻胶芯(H2.0)	LCP UL94V-0 本色
2	0.5后翻端子(H2.0)	铜合金/表面点镀金
3	0.5后翻后盖(H2.0)	LCP UL94V-0 黑色
4	0.5后翻焊片(H2.0)	铜合金/表面镀锡

适用扁平线(Applicable Flat Cable)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~+85°C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: ≤0.03Ω.
5. 绝缘电阻: ≥500MΩ

适用线路板(PCB LAYOUT)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X°±5°	PART NO.	TITLE: 0.5 Pitch H2.0		
.XX±0.20	.XX°±2°	JXT-AFC05-HFNP-H20	Backflip R/A Type CONN		
.XXX±0.05	.XXX°±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---		SCALE	SHEET	
			N:A	1/1	