




2P



3P~16P



**Ordering Information:**

A2008H-XP - \*\*\* - \*\*\*  
1 2 3

1.Part NO.

2.Material:

(Blank):Nylon 66,UL94V-0(White)

GWT: Nylon 66,UL94V-0(Beige),IEC 60335-1,5th Edition  
Glow Wire Capable.

3.Color:

(Blank): see section 2 material

BL: Blue


YL: Yellow

BK: Black

GN: Green

RD: Red

GY: Gray



**SPECIFICATIONS:**

Current Rating: 2A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 30mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 1000V AC/minute

**Ordering Information & Dimensions**

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.00	5.50	3.20	12P	22.00	25.50	16.30
3P	4.00	7.50	3.20	13P	24.00	27.50	16.30
4P	6.00	9.50	4.30	14P	26.00	29.50	16.30
5P	8.00	11.50	4.30	15P	28.00	31.50	16.30
6P	10.00	13.50	8.30	16P	30.00	33.50	16.30
7P	12.00	15.50	10.30	17P	32.00	35.50	16.30
8P	14.00	17.50	12.30	18P	34.00	37.50	16.30
9P	16.00	19.50	12.30	19P	36.00	39.50	16.30
10P	18.00	21.50	12.30	20P	38.00	41.50	16.30
11P	20.00	23.50	16.30				



CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE
mm	4:1	1 of 1	2.00mm PITCH HOUSING
DRAWN	CHK'D	APPR	
Chengbiao Ye	Djankui Wan	Jack Yin	

General Tolerances	THIRD ANGLE PROJECTION
x,xx±0.25	
x.xxx±0.20	
x,xxxx±0.15	
ANGLES ±1°	

DRAWING NO.	REV
A2008H-XP	A2

A2	CHANGE THE DRAWING	2023.06.08
A1	CHANGE THE DRAWING	2020.09.19
A0	NEW RELEASE	2020.09.19
REV	DESCRIPTION	DATE