

Specification Sheet

Part Number: CTP120STD



Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install
Tubing provides full coverage where spiral wrap or other coverings may not be suitable

In harsh applications the tubing can provide resistance to crushing, impact, and abrasion

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires

Convoluted Tubing, Slit, 0.5" Dia, PE, Black, 1100 ft/carton

Article Number	169-60507
Type	CTP120
Color	Black (BK)
Quantity Per	carton

Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
Short Description	Convoluted Tubing, Slit, 0.5" Dia, PE, Black, 1100 ft/carton
Global Part Name	CTP120-PE-BK
Length L (Imperial)	1100.0
Length L (Metric)	335.3
Variant	Slit
Inner Diameter D (Imperial)	0.516
Inner Diameter D (Metric)	13.11
Diameter D (Imperial)	0.70
Diameter D (Metric)	17.78
Outside Diameter OD (Imperial)	0.70
Outside Diameter OD (Metric)	17.78
Nominal Diameter (Imperial)	0.5

Nominal Diameter (Metric)	12.70
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene (PE)
Material Shortcut	PE
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1100
Package Quantity (Metric)	335.30
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)