






ORDER NO.	WOODHEAD NO.	COLOR
130142-0041	2882	YELLOW



WIRING TERMINATION



* FOR SCREW TORQUE, SEE ASSEMBLY INSTRUCTIONS

ITEM NO.	DESCRIPTIONS	MATERIAL	QTY.
1	GROUND PIN	BRASS	1
2	BLADES	BRASS, NICKEL PLATED	4
3	RETAINING SCREWS	STAINLESS STEEL	2
4	TERMINAL SCREWS/CLAMP ASSEMBLY	BRASS, ZINC PLATED	4
5	INSERT; WHITE	NYLON	1
6	TERMINAL COVER	POLYCARBONATE	1
7	SET SCREW	STAINLESS STEEL	1
8	HOUSING; YELLOW	NYLON	1
9	CLAMP SUPPORT	NYLON	1
10	CLAMP CORD MALE; YELLOW	NYLON	1
11	CLAMP CORD INSERT	NYLON	1
12	CLAMP CORD FEMALE; YELLOW	NYLON	1
13	RETAINING SCREWS	STAINLESS STEEL	2

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: NEW RELEASE				
	DIMENSION UNITS	SCALE					
▽ = 0	INCH[mm]	NTS	EC NO: 628448		SUPER-SAFEWAY PLUG NEMA 4P5W L22-30P		
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: VHANDI 2019/06/10				
▽ = 0			CHK'D: DNGUYEN62 2020/02/14		PRODUCT CUSTOMER DRAWING		
▽ = 0			APPR: HKNEELAND 2020/06/02				
▽ = 0			INITIAL REVISION:		DOCUMENT NUMBER		
▽ = 0			DRWN: DRWN BY				
▽ = 0			APPR: APPR BY		DOC TYPE DOC PART REVISION		
▽ = 0			ANGULAR TOL ± °				
▽ = 0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NUMBER CUSTOMER SHEET NUMBER		
▽ = 0			THIRD ANGLE PROJECTION				
▽ = 0			DRAWING SERIES		B-SIZE 130142		