

修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW DWG		

	A	B	C	D
2P	5.60	4.60	2.00	
3P	7.60	6.60	4.00	2.85
4P	9.60	8.60	6.00	4.85
5P	11.60	10.60	8.00	6.85
6P	13.60	12.60	10.00	8.85
7P	15.60	14.60	12.00	10.85
8P	17.60	16.60	14.00	12.85
9P	19.60	18.60	16.00	14.85
10P	21.60	20.60	18.00	16.85
11P	23.60	22.60	20.00	18.85
12P	25.60	24.60	22.00	20.85
13P	27.60	26.60	24.00	22.85
14P	29.60	28.60	26.00	24.85
15P	31.60	30.60	28.00	26.85
16P	33.60	32.60	30.00	28.85

产品要求:

1、材质: 白色PA66 UL94-V0;

2、外观: 无变形、缺胶、披锋 $\leq 0.08\text{mm}$;

3、尺寸: 所有尺寸均符合检测标准。




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: SMH200-NN

X.X ± 0.30 X.X* $\pm 3^\circ$

APPD:
核准: 谢亮

PART NO:
产品编号: SMH200-NN-HDGC2008

X.XX ± 0.30 X.XX* $\pm 2^\circ$

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ± 0.10 X.XXX* $\pm 1^\circ$

DRAW:
绘图: 黄艳兰

1:1 mm A001