

| PART NUMBER | CKTS | QUANTITY PER BAG | BAGS PER CARTON | PARTS PER CARTON (SPQ) | MOISTURIZATION METHOD △1 | PANEL LOCK |
|---|---|---|---|---|---|---|
| 215922-02*1 | 2 | 3000 | 4 | 12000 | NO MOISTURIZATION | WITHOUT |
| 215922-04*1 | 4 | 2600 | 4 | 10400 | | |
| 215922-06*1 | 6 | 2000 | 4 | 8000 | | |
| 215922-08*1 | 8 | 1700 | 4 | 6800 | | |
| 215922-10*1 | 10 | 1400 | 4 | 5600 | | |
| 215922-12*1 | 12 | 1000 | 4 | 4000 | | |
| 215922-1401 | 14 | 800 | 4 | 3200 | | |
| 215922-1601 | 16 | 800 | 4 | 3200 | | |
| 215922-1801 | 18 | 600 | 4 | 2400 | | |
| 215922-2001 | 20 | 600 | 4 | 2400 | | |
| 215922-2201 | 22 | 600 | 4 | 2400 | | |
| 215922-2401 | 24 | 450 | 4 | 1800 | | |
| 215922-02*0 | 2 | 2000 | 4 | 8000 | SEE SHEET 2 | WITH |
| 215922-04*0 | 4 | 1800 | 4 | 7200 | | |
| 215922-06*0 | 6 | 1600 | 4 | 6400 | | |
| 215922-08*0 | 8 | 1100 | 4 | 4400 | | |
| 215922-10*0 | 10 | 1000 | 4 | 4000 | | |
| 215922-12*0 | 12 | 900 | 4 | 3600 | | |
| 215922-1400 | 14 | 800 | 4 | 3200 | | |
| 215922-1600 | 16 | 700 | 4 | 2800 | | |
| 215922-1800 | 18 | 600 | 4 | 2400 | | |
| 215922-2000 | 20 | 600 | 4 | 2400 | | |
| 215922-2200 | 22 | 400 | 4 | 1600 | | |
| 215922-2400 | 24 | 350 | 4 | 1400 | | |


TBD: NO PRODUCTION, TO BE ADDED AFTER BEING PRODUCED.




BUBBLE PAPER:
88596-1546




BAG:
96713-0003
(DETAILS REFER
TO SHEET 2)



INNER CARTON
313005940 OR 885961537
2CELL DIVIDER
QTY(2)



BUBBLE PAPER:
88596-1546



CARTON:
88596-1483

LEGEND

206461 - X X X X

- 0 - PANEL MOUNT
  1 - FREE HANGING
- POLARIZATION / COLOR
  0- BLACK
  1 - NATURAL
  2 - RED
  3 - BLUE
  4- YELLOW
- CKT SIZE 02-24

NOTES:

△1. MOISTURIZATION METHOD DESCRIPTIONG REFER TO SHEET 2.

2. STANDARD PAKAGE QUANTITY(SPQ) SEE ABOVE CHART.

3. PACKAGE WAY FOLOW RIGHT ILLUSTRATION.

4. ALL PAKAGE MATERIAL AND PRODUCT COMPLIANT TO RoHS DIRECTIVE 2011/65/EU AND ELV DIRECTIVE 2000/53/EV.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS: FA = 0, FC = 0, FP = 0

DIVISIONAL SYMBOLS

DIMENSION UNITS: mm | SCALE: 1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | |
|---|---|
| ANGULAR TOL | ± ° |
| 4 PLACES | ± |
| 3 PLACES | ± 0.1 |
| 2 PLACES | ± 0.3 |
| 1 PLACE | ± 0.5 |
| 0 PLACES | ± |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 736922
DRWN: VENKAS5 2023/01/18
CHK'D: VENKAS5 2023/02/03
APPR: MRAMAKRISHNA 2023/02/03

INITIAL REVISION:
DRWN: GLLI 2021/10/28
APPR: XQZHANG 2021/11/15

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 215922

molex

PACKING SPEC FOR MICRO-FIT PLUS WTW HSG

PRODUCT CUSTOMER DRAWING


| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-PK | PSD | 000 | C |

| MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|
| | | 1 OF 2 |

| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/07/19 06:20:25 |
|---|---|---|---|

FORMAT: master-ib-prod-A3
REVISION: J1
DATE: 2021/05/01

## MOISTURIZATION METHOD




DETAILED MOISTURIZATION METHOD REFER TO AS-45499-001.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

| | |
|---|---|
| FUNCTIONAL SYMBOLS | FA = 0, FC = 0, FP = 0 |
| DIVISIONAL SYMBOLS | |
| DIMENSION UNITS | mm |
| SCALE | 1:1 |
| GENERAL TOLERANCES (UNLESS SPECIFIED) | |
| ANGULAR TOL | ± ° |
| 4 PLACES | ± |
| 3 PLACES | ± 0.1 |
| 2 PLACES | ± 0.3 |
| 1 PLACE | ± 0.5 |
| 0 PLACES | ± |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | |

CURRENT REV DESC:

EC NO: 736922
DRWN: VENKAS5 2023/01/18
CHK'D: VENKAS5 2023/02/03
APPR: MRAMAKRISHNA 2023/02/03

INITIAL REVISION:
DRWN: GLLI 2021/10/28
APPR: XQZHANG 2021/11/15

molex

PACKING SPEC FOR MICRO-FIT PLUS WTW HSG

PRODUCT CUSTOMER DRAWING


| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-PK | PSD | 000 | C |


| THIRD ANGLE PROJECTION | DRAWING | SERIES | MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|---|---|---|
| | A3-SIZE | 215922 | | | 2 OF 2 |


| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/07/19 06:20:25 |
|---|---|---|---|


FORMAT: master-tb-prod-A3
REVISION: J1
DATE: 2021/05/01


# FREE HANGING PLUG PARTS




| DIM'A' | DIM'B' | CKT SIZE |
|---|---|---|
| 3.85 | 5.45 | 2 |
| 6.85 | 8.45 | 4 |
| 9.85 | 11.45 | 6 |
| 12.85 | 14.45 | 8 |
| 15.85 | 17.45 | 10 |
| 18.85 | 20.45 | 12 |
| 21.85 | 23.45 | 14 |
| 24.85 | 26.45 | 16 |
| 27.85 | 29.45 | 18 |
| 30.85 | 32.45 | 20 |
| 33.85 | 35.45 | 22 |
| 36.85 | 38.45 | 24 |

NOTES:
1. MATERIAL: PA66, 94V-0, COLOR : SEE TABLE IN SHEET 5
2. PRODUCT SPECIFICATION: 2159530000-PS.
3. PACKAGE SPECIFICATION: 2159220000-PK.
4. TO USE WITH TERMINAL OF 2015953-****.
5. TO USE WITH TPA OF 206462-****.
6. TO MATE WITH RECEPTACLE OF 206461-****.
7. PARTS CONFORM TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/08/24 11:19:06 |
|---|---|---|---|

FORMAT: master-lb-prod-A3
REVISION: J1
DATE: 2021/05/01

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FD = 0
DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

| DIMENSION UNITS | SCALE |
|---|---|
| mm | 1:1 |

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | | |
|---|---|---|
| ANGULAR TOL | ± | ° |
| 4 PLACES | ± | |
| 3 PLACES | ± | |
| 2 PLACES | ± | 0.2 |
| 1 PLACE | ± | 0.3 |
| 0 PLACES | ± | |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 760703
DRWN: VENKAS5 2023/02/28
CHK'D: VENKAS5 2023/08/24
APPR: MRAMAKRISHNA 2023/08/24

INITIAL REVISION:
DRWN: GLLI 2021/01/29
APPR: XQZHANG 2021/11/15

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 215922

molex


PLUG HOUSING OF MICRO-FIT PLUS WTW DR POWER CONNECTOR


PRODUCT CUSTOMER DRAWING


| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-SD | PSD | 000 | B |


| MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|
| | GENERAL MARKET | 1 OF 6 |

# FREE HANGING PLUG PARTS



TERMINAL AND TPA ORIENTATION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

| | | | |
|---|---|---|---|
| FUNCTIONAL SYMBOLS | FA = 0 | DIMENSION UNITS | mm |
| | FC = 0 | SCALE | 1:1 |
| | FP = 0 | GENERAL TOLERANCES (UNLESS SPECIFIED) | |
| DIVISIONAL SYMBOLS | | ANGULAR TOL ± ° | |
| | | 4 PLACES ± | |
| | | 3 PLACES ± | |
| | | 2 PLACES ± 0.2 | |
| | | 1 PLACE ± 0.3 | |
| | | 0 PLACES ± | |
| | | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | |

CURRENT REV DESC:

EC NO: 760703
DRWN: VENKAS5 2023/02/28
CHK'D: VENKAS5 2023/08/24
APPR: MRAMAKRISHNA 2023/08/24

INITIAL REVISION:
DRWN: GLLI 2021/01/29
APPR: XQZHANG 2021/11/15

molex

PLUG HOUSING OF MICRO-FIT PLUS WTW DR POWER CONNECTOR

PRODUCT CUSTOMER DRAWING


| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-SD | PSD | 000 | B |

| THIRD ANGLE PROJECTION | DRAWING | SERIES | MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|---|---|---|
| | A3-SIZE | 215922 | | GENERAL MARKET | 2 OF 6 |


| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/08/24 11:19:06 |
|---|---|---|---|


FORMAT: master-tb-prod-A3
REVISION: J1
DATE: 2021/05/01

# PANEL MOUNT PLUG PARTS






MOLEX LOGO





MOLEX SERIES NUMBER




RECOMMENDED PANEL CUT OUT
(TOLERRANCE +/-0.05 THICKNESS=1.2~2.2MM)

| DIM 'A' | DIM 'C' | DIM 'D' | DIM 'E' | DIM 'F' | CKT SIZE |
|---|---|---|---|---|---|
| 3.85 | 6.25 | 10.77 | 8.77 | 4.15 | 2 |
| 6.85 | 9.25 | 13.77 | 11.77 | 7.15 | 4 |
| 9.85 | 12.25 | 16.77 | 14.77 | 10.15 | 6 |
| 12.85 | 15.25 | 19.77 | 17.77 | 13.15 | 8 |
| 15.85 | 18.25 | 22.77 | 20.77 | 16.15 | 10 |
| 18.85 | 21.25 | 25.77 | 23.77 | 19.15 | 12 |
| 21.85 | 24.25 | 28.77 | 26.77 | 22.15 | 14 |
| 24.85 | 27.25 | 31.77 | 29.77 | 25.15 | 16 |
| 27.85 | 30.25 | 34.77 | 32.77 | 28.15 | 18 |
| 30.85 | 33.25 | 37.77 | 35.77 | 31.15 | 20 |
| 33.85 | 36.25 | 40.77 | 38.77 | 34.15 | 22 |
| 36.85 | 39.25 | 43.77 | 41.77 | 37.15 | 24 |

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FD = 0

DIVISIONAL SYMBOLS

| DIMENSION UNITS | SCALE |
|---|---|
| mm | 1:1 |

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | |
|---|---|
| ANGULAR TOL | ± ° |
| 4 PLACES | ± |
| 3 PLACES | ± |
| 2 PLACES | ± 0.2 |
| 1 PLACE | ± 0.3 |
| 0 PLACES | ± |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 760703
DRWN: VENKAS5 2023/02/28
CHK'D: VENKAS5 2023/08/24
APPR: MRAMAKRISHNA 2023/08/24

INITIAL REVISION:
DRWN: GLLI 2021/01/29
APPR: XQZHANG 2021/11/15

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 215922

molex

PLUG HOUSING OF MICRO-FIT PLUS WTW DR POWER CONNECTOR

PRODUCT CUSTOMER DRAWING


| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-SD | PSD | 000 | B |


| MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|
| | GENERAL MARKET | 3 OF 6 |

| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/08/24 11:19:06 |
|---|---|---|---|

FORMAT: master-ib-prod-A3
REVISION: J1
DATE: 2021/05/01

# PANEL MOUNT PLUG PARTS




TERMINAL AND TPA ORIENTATION

| | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|
| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/08/24 | 11:19:06 | | | | | | |

FORMAT: master-tb-prod-A3
REVISION: J1
DATE: 2021/05/01

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FD = 0
DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

| DIMENSION UNITS | SCALE |
|---|---|
| mm | 1:1 |

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | | |
|---|---|---|
| ANGULAR TOL | ± | ° |
| 4 PLACES | ± | |
| 3 PLACES | ± | |
| 2 PLACES | ± | 0.2 |
| 1 PLACE | ± | 0.3 |
| 0 PLACES | ± | |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 760703
DRWN: VENKAS5 2023/02/28
CHK'D: VENKAS5 2023/08/24
APPR: MRAMAKRISHNA 2023/08/24

INITIAL REVISION:
DRWN: GLLI 2021/01/29
APPR: XQZHANG 2021/11/15

| THIRD ANGLE PROJECTION | DRAWING | SERIES |
|---|---|---|
| | A3-SIZE | 215922 |

molex

PLUG HOUSING OF MICRO-FIT PLUS WTW DR POWER CONNECTOR

PRODUCT CUSTOMER DRAWING

| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-SD | PSD | 000 | B |

| MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|
| | GENERAL MARKET | 4 OF 6 |

| FREE HANGING | | | |
|---|---|---|---|
| PART NUMBER | CKT | POLARIZATION | COLOR |
| 215922-0201 | 2 | A | BLACK |
| 215922-0211 | | B | NATURAL |
| 215922-0221 | | C | RED |
| 215922-0231 | | D | BLUE |
| 215922-0241 | | E | YELLOW |
| 215922-0401 | 4 | A | BLACK |
| 215922-0411 | | B | NATURAL |
| 215922-0421 | | C | RED |
| 215922-0431 | | D | BLUE |
| 215922-0441 | | E | YELLOW |
| 215922-0601 | 6 | A | BLACK |
| 215922-0611 | | B | NATURAL |
| 215922-0621 | | C | RED |
| 215922-0631 | | D | BLUE |
| 215922-0641 | | E | YELLOW |
| 215922-0801 | 8 | A | BLACK |
| 215922-0811 | | B | NATURAL |
| 215922-0821 | | C | RED |
| 215922-0831 | | D | BLUE |
| 215922-0841 | | E | YELLOW |
| 215922-1001 | 10 | A | BLACK |
| 215922-1011 | | B | NATURAL |
| 215922-1021 | | C | RED |
| 215922-1031 | | D | BLUE |
| 215922-1041 | | E | YELLOW |
| 215922-1201 | 12 | A | BLACK |
| 215922-1211 | | B | NATURAL |
| 215922-1221 | | C | RED |
| 215922-1231 | | D | BLUE |
| 215922-1241 | | E | YELLOW |
| 215922-1401 | 14 | A | BLACK |
| 215922-1601 | 16 | A | BLACK |
| 215922-1801 | 18 | A | BLACK |
| 215922-2001 | 20 | A | BLACK |
| 215922-2201 | 22 | A | BLACK |
| 215922-2401 | 24 | A | BLACK |

| PANEL MOUNT | | | |
|---|---|---|---|
| PART NUMBER | CKT | POLARIZATION | COLOR |
| 215922-0200 | 2 | A | BLACK |
| 2159220210 | | B | NATURAL |
| 2159220220 | | C | RED |
| 2159220230 | | D | BLUE |
| 2159220240 | | E | YELLOW |
| 215922-0400 | 4 | A | BLACK |
| 2159220410 | | B | NATURAL |
| 2159220420 | | C | RED |
| 2159220430 | | D | BLUE |
| 2159220440 | | E | YELLOW |
| 215922-0600 | 6 | A | BLACK |
| 2159220610 | | B | NATURAL |
| 2159220620 | | C | RED |
| 2159220630 | | D | BLUE |
| 2159220640 | | E | YELLOW |
| 215922-0800 | 8 | A | BLACK |
| 2159220810 | | B | NATURAL |
| 2159220820 | | C | RED |
| 2159220830 | | D | BLUE |
| 2159220840 | | E | YELLOW |
| 215922-1000 | 10 | A | BLACK |
| 2159221010 | | B | NATURAL |
| 2159221020 | | C | RED |
| 2159221030 | | D | BLUE |
| 2159221040 | | E | YELLOW |
| 215922-1200 | 12 | A | BLACK |
| 2159221210 | | B | NATURAL |
| 2159221220 | | C | RED |
| 2159221230 | | D | BLUE |
| 2159221240 | | E | YELLOW |
| 215922-1400 | 14 | A | BLACK |
| 215922-1600 | 16 | A | BLACK |
| 215922-1800 | 18 | A | BLACK |
| 215922-2000 | 20 | A | BLACK |
| 215922-2200 | 22 | A | BLACK |
| 215922-2400 | 24 | A | BLACK |

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FD = 0
DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

| DIMENSION UNITS | SCALE |
|---|---|
| mm | 1:1 |

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | |
|---|---|
| ANGULAR TOL | ± ° |
| 4 PLACES | ± |
| 3 PLACES | ± |
| 2 PLACES | ± 0.2 |
| 1 PLACE | ± 0.3 |
| 0 PLACES | ± |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 760703
DRWN: VENKAS5 2023/02/28
CHK'D: VENKAS5 2023/08/24
APPR: MRAMAKRISHNA 2023/08/24

INITIAL REVISION:
DRWN: GLLI 2021/01/29
APPR: XQZHANG 2021/11/15

molex

PLUG HOUSING OF MICRO-FIT PLUS WTW DR POWER CONNECTOR































PRODUCT CUSTOMER DRAWING







| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-SD | PSD | 000 | B |

| THIRD ANGLE PROJECTION | DRAWING | SERIES | MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|---|---|---|
| | A3-SIZE | 215922 | | GENERAL MARKET | 5 OF 6 |

| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/08/24 11:19:06 |
|---|---|---|---|

FORMAT: master-lb-prod-A3
REVISION: J1
DATE: 2021/05/01

| CKT | POLARIZATION "A"- BLACK | POLARIZATION "B" - NATURAL | POLARIZATION "C" - RED | POLARIZATION "D" - BLUE | POLARIZATION "E" - YELLOW |
|---|---|---|---|---|---|
| 2 |  |  |  |  |  |
| 4 |  |  |  |  |  |
| 6 |  |  |  |  |  |
| 8 |  |  |  |  |  |
| 10 |  |  |  |  |  |
| 12 |  |  |  |  |  |

| CKT | POLARIZATION "A"- BLACK |
|---|---|
| 14 |  |
| 16 |  |
| 18 |  |
| 20 |  |
| 22 |  |
| 24 |  |

| | | | |
|---|---|---|---|
| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/03/06 08:44:47 |

FORMAT: master-tb-prod-A2
REVISION: J1
DATE: 2021/05/01

| FUNCTIONAL SYMBOLS | |
|---|---|
| FA | = 0 |
| FC | = 0 |
| FP | = 0 |
| DIVISIONAL SYMBOLS | |

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

| DIMENSION UNITS | SCALE |
|---|---|
| mm | 3:1 |

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | | |
|---|---|---|
| ANGULAR TOL | ± | ° |
| 4 PLACES | ± | |
| 3 PLACES | ± | |
| 2 PLACES | ± | 0.2 |
| 1 PLACE | ± | 0.3 |
| 0 PLACES | ± | |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 760703

| | | |
|---|---|---|
| DRWN: | VENKAS5 | 2023/02/28 |
| CHK'D: | VENKAS5 | 2023/08/24 |
| APPR: | MRAMAKRISHNA | 2023/08/24 |

INITIAL REVISION:

| | | |
|---|---|---|
| DRWN: | GLLI | 2021/01/29 |
| APPR: | XQZHANG | 2021/11/15 |

THIRD ANGLE PROJECTION

| DRAWING | SERIES |
|---|---|
| A2-SIZE | 215922 |

molex

PLUG HOUSING OF MICRO-FIT PLUS WTW DR POWER CONNECTOR

PRODUCT CUSTOMER DRAWING

| DOCUMENT NUMBER | DOC TYPE | DOC PART | REVISION |
|---|---|---|---|
| 2159220000-SD | PSD | 000 | B |

| MATERIAL NUMBER | CUSTOMER | SHEET NUMBER |
|---|---|---|
| SEE CHART IN LAST SHEET | GENERAL MARKET | 6 OF 6 |