KC-22/12VDC Product Details



KC-22/12VDC
(5-1618278-9)
TE Internal Number: 5-1618278-9
Obsolete
Contact Product Information Center

High Voltage Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = Make Only, Yes, No
- Contact Current Rating = 0 - 65 Amps.
- Not RF Rated
- Coil Voltage = 12 VDC

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Termination Style = Turret Terminal

Electrical Characteristics:
- Contact Current Rating (Amps.) = 0 – 65
- RF Rated = No
- Coil Voltage (VDC) = 12
- Voltage, Max. (VDC) = 0 – 25000
- Current, Carry Only = Yes

Termination Related Features:
- High Voltage Connection (Power) = Bifurcated Terminals
- High Voltage Connection (Coil) = Turret Terminals
- Auxiliary Contacts = Without

Body Related Features:
- Mount Style = Threaded

Configuration Related Features:
- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = Make Only, Yes, No
- Economizer = Without

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not suitable for lead free processing

Other:
- Brand = Kilovac

© 2009 Tyco Electronics All Rights Reserved | Privacy Policy