This document was generated on 12/31/2022


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0150180235

Status: Active

Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Description: 0.50mm Pitch Premo-Flex FFC Jumper with Ears, Same Side Contacts (Type A), 127.00mm Cable Length, Gold (Au) Plating, 22 Circuits



Series image - Reference only

Documents:

Drawing (PDF)
Datasheet (PDF)
Product Specification 150180001-000 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	15018
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
Taxonomy	Flexible Printed Circuit (FPC)
UPC	193264330690

Physical

Cable Length	127.00mm
Circuits (Loaded)	22
Contact Layout Type	A (same side)
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Product Specification	150180001-000
Sales Drawing	SD-15018-001-001

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ECHA_01_2020 (16 January 2020

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
15018 Series

Mates With
Easy-On FFC/FPC Connector 5051102291

This document was generated on 12/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION