

1		2			3			4		5		6		7		8			
linear dimension(Tolerances Standard GB/T 14486-2008)								—	$\square$	$\perp$	版本 Version		描述 Description	设计 Design	批准 Approved	日期 Date			
A	variable range	to	over	over	over	over	over	to	over	over	A		新发行	熊武敌	楼特高	2024.03.10			
	tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60								
B																	材质及电镀 MATERIAL		
C																	螺丝 Screws		M2.5, 钢, 镀锌 M2.5, Steel, Zn plated
D																	夹片 Clamp		铜合金, 镀镍 Copper alloy, Ni plated
E																	方块 Cage		铜合金, 镀镍 Copper alloy, Ni plated
F																	塑件 Housing		PA66, UL94V-0
G																	电气性能 ELECTRICAL		
H																	参考标准 Stanard		UL IEC
																	额定电压 Rated voltage		300V 320V
	额定电流 Rated current		10A 15A																
	使用线径 Wire range		24-12AWG 2.5mm <sup>2</sup>																
	接触电阻 Contact resistance		20mΩ																
	绝缘电阻 Insulation resistance		500MΩ/DC500V																
	耐电压 Withstanding voltage		AC1600V/1Min																
	机械性能 MECHANICAL																		
	温度范围 Temp. range		-40℃ ~ +105℃																
	瞬时温度 Max. soldering		+250℃ for 5 Sec																
	扭矩 Torque		4.08kgf. cm/0.4N. m																
	剥线长度 Strip length		7~8mm																
	编码原则(Product Number Code): <b>WJ2EDGKB-5.08-XXP-1Y-00A</b> 产品型号(Series No.)   间距(Pitch)   极数(No. of Poles)   塑体颜色(Housing Color)   客户需求(Customer Request)																		
	1: 单倍间距 (Single Pitch)   2: 双倍间距 (Double Pitch)   1: 灰色(Grey)   2: 蓝色(Blue)   3: 黑色(Black)   4: 绿色(Green)   5: 橙色(Orange)   6: 红色(Red)   7: 透明(Transparent)   8: 黄色(Yellow)   9: 白色(White)																		
	第三视角 (THIRD ANGLE PROJECTION)												插拔式接线端子 PLUG-IN TERMINAL BLOCK						
	图纸类型 (TYPE)				CUSTOMER DRAWING				型号 (NAME)		WJ2EDGKB-5.08-XXP-1Y-00A								
	单位 (UNITS)		mm		版本 (VERSION)		A												
	尺寸 (SIZE)		A4																
	比例 (SCALE)		1:1																
	图页 (SHEET)		1/1																
	宁波康奈克斯电气有限公司 NINGBO KANGNEX ELECTRIC., LTD.																		