





SCHEMATIC

PCB LAYOUT
TOP VIEW

PIN	Ø2.0	Ø2.5	
APPD.			

					TOLERANCE UNLESS SPECIFIED					
6	COVER	PBT			UP TO 5mm: ±0.1	ANGULAR	1	2017.3.8	增加重量尺寸	
5	CONTACT FOOT	BRASS	1	Sn-PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY APPD
4	PIN	BRASS	1	Ni-PLATED	TITLE: DC JACK					
3	SPRING	STEEL/PBS	1	Sn-PLATED	MODEL: DC-016-2.5-PU (HY)					
2	FLAT PIECE	BRASS	1	Sn-PLATED	UNIT : MM					ROHS COMPLIANT
1	HOUSING	PBT	1		SCALE: 1:1					CHK'D
					HAOYU(HONGKONG)LIMITED					APPD
					皓宇(香港)有限公司					PRO.AGL:
NO.	PART	NAME	MATERIAL	QTY	FINISHING					