



SIGN	DATE	DESCRIPTION	APPROVER
⚠			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!









P.C.B. LAYOUT

Material:

- Item ⓐ Terminal(housing): Thermoplastic (UL94V-0)
- Item ⓑ Contact pin: Brass,Bright Tin plated over Nickel plated

Electrical:	cULus
Voltage rating:	300V
Current rating:	10A
Withstanding Voltage:	1.6KV
Operating temperature:	-40°C to +115°C
Soldering temperature:	260°C±5°C/5 Sec
Safety Approval:	cULus
Critical dimension:	▽



ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OP-3.5mm series (L=12.5 ø1.0)				
PART NO.	OP04220000001G			DWG NO.	80P0117
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Evan 11/19-15	Evan 11/03-15	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: B	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°