






P.C. MOUNTING




NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA @12VDC
- ▲ 5. CONTACT MATERIAL: SILVER
6. TRAVEL: 0.30 ± 0.15 mm
- ▲ 7. OPERATING FORCE: 160 ± 50 gf
8. CONTACT RESISTANCE: 100m Ω MAX.
9. ELECTRICAL LIFE: 100,000 CYCLES MIN
10. ▲ DENOTES CRITICAL DIMENSION



▲ SWITCH
TL1100CF160Q
(P001110)

▲ CAP
COLOR: BLUE
320.08BLU
(B099406)



TITLE TL1100CF160Q.08BLU

A	24744	RELEASE	2/17/21	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
3:1	2/11/2021	MW	XP0323P	A