




REV.	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		




3D View

Specification

- Voltage Rating : 30V AC/DC
- Current Rating : 0.5A(32AWG) / 0.2A(36AWG) AC/DC
- Withstanding Voltage : 200V AC /minute
- Insulation Resistance : ≥100MΩ
- Temperature Range : - 25°C to + 85°C
- Contact Resistance : ≤20mΩ
- After Environmental Testing: ≤40mΩ
- Suitable Wire/Cable:AWG #32 to #36,OD:0.39mm max

Ordering Information

- 1.Category:W-Wafer
- 2.Soldering PCB Angle:R-Right angle/90°
- 3.Soldering method:S-SMD/SMT,Surface Mount Technology
- 4.Number of rows&pins:XX
- 5.Plug the pin & Special No.:Blank-Ordinary;S-with Slot
- 6.Material(Insulators):LP-LCP,UL94V-0;4T-PA4T,UL94V-0
- 7.Color:Blank-Natural;BK-Black
- 8.Environmental protection Standard:Blank-Ordinary
RoHS;HF-Halogen Free
- 9.Material(Pin):PB-Phosphor Bronze
- 10.Plating :SN-Bright Tin Plated;AU-Gold flash;AU3-Gold 3U"
- 11.Package:Blank-Tape&Reel,SPQ:3.5K/reel preferred



Recommended P.C.B Layout
General Tolerance±0.05

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	0.80	1.90	3.78	12	8.80	9.90	11.78
03	1.60	2.70	4.58	13	9.60	10.70	12.58
04	2.40	3.50	5.38	14	10.40	11.50	13.38
05	3.20	4.30	6.18	15	11.20	12.30	14.18
06	4.00	5.10	6.98	16	12.00	13.10	14.98
07	4.80	5.90	7.78	17	12.80	13.90	15.78
08	5.60	6.70	8.58	18	13.60	14.70	16.58
09	6.40	7.50	9.38	19	14.40	15.50	17.38
10	7.20	8.30	10.18	20	15.20	16.30	18.18
11	8.00	9.10	10.98				

DESIGN:		Xiping Huang			广东国连电子有限公司				
CHECK:		Ke Tian			GUANGDONG GUOLIAN ELECTRONICS CO.,LTD				
APPROVED:		Youquan Xu		TITLE:					
DIM	TOL	DIM	TOL	0.8卧贴					
X.	±0.25			PART NO.					
X. X	±0.20			A0800WR-S-NP-***					
X. XX	±0.15			REV. A					
X. XXX				SCALE: N/A					
				UNIT:		SHEET:			
				mm		1/1			