




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24




- SPECIFICATIONS**
- Current rating: 7A
 - Temperature range: -40°C ~ +105°C
 - Insulation resistance: 1000MΩ Min.
 - Withstanding voltage: 1500V AC/ minute.
 - Contact resistance: 20mΩ Max.

Material:
 Insulator Material:LCP/ (UL 94V-0)
 Contact Material:Phosphor Bronze
 Plating:Gold/Tin Over Nickel
 Mate with XFCN PZ508 Single row series

Ordering Code:
 PM508V-11-XX-H889
 1 2
 1.序列号
 2.Pin位数: 02-20P

No.of PIN/ROW	Dimension	
	A	B
02	10.16	5.08
03	15.24	10.16
04	20.32	15.24
05	25.40	20.32
06	30.48	25.40
07	35.56	30.48
08	40.64	35.56
09	45.72	40.64
10	50.80	45.72
11	55.88	50.80
12	60.96	55.88
13	66.04	60.96
14	71.12	66.04
15	76.20	71.12
16	81.28	76.20
17	86.36	81.28
18	91.44	86.36
19	96.52	91.44
20	101.60	96.52



P.C.B Hole Layout

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: PM508V-11-XX-H889	
TITLE: 5.08mm Female Header Connectors	
APPD	Chen ZhiQiang
CHKD	Liu Wei
DRAW	Chen HongJiang
DATE	2024.09.27

XFCN 兴飞连接器	
0769-82001899	
www.xfconn.com	
DWG NO: /	
VIEW	
SCALE	SHEET REV
NONE	1/1 A1