
Data sheet

27108.3 PAP 4/4A OG



End plate, Width: 1.5 mm, Colour: Orange

Business data

Article number	27108.3
Article name	PAP 4/4A OG
GTIN (EAN)	4044211224677
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	2.5 g
Weight per piece (including packaging)	2.7 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27108.6
Product description	End plate

Data sheet

27108.3 PAP 4/4A OG

Technical data

Dimensions

Length	77 mm
Width	1.5 mm
Height	28.7 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Candidate Substance Note	No

Data sheet
27108.3 PAP 4/4A OG

Media

Data sheet
27108.3 PAP 4/4A OG


Accessories

Terminal blocks



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
27017.2	PSL 4/4A GNYE	4044211215880	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Grey


Article number	Article name	GTIN (EAN)	Packaging unit
27016.6	PRK 4/4A GR	4044211215873	50

##INVERSE##CONTA-CONNECT



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
27017.2	PSL 4/4A GNYE	4044211215880	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
27016.6	PRK 4/4A GR	4044211215873	50