

図面番号(DRAWING NO.) SJ103088

版数 REV.	年月日 DATE	DCN NO.	変更内容 DESCRIPTION	製図 DR.	担当 CHK.	査閲 APPD.	承認 APPD.
2	13.Oct.2005	058374	REVISED NOTE6		Y.TAKAGI	A.Sago	Y.Kubota






エクストラクションツール
（添付品）


SHALL SEPARATELY FORM

FRONT INTERFACE




REAR INTERFACE






SECT. A−A
(SCALE 5:1)




SECT. B−B
(SCALE 5:1)


PART No.	±0.5 A	±0.25 B	±0.25 B'	±0.13 C	±0.25 D	±0.25 D'	±0.5 E	F	G	H	J
DEMA- 9P−FOR	30.8	——	16.90	24.99	——	8.34	12.6	19.3	10.7	1.2	0.8
DEMA- 9S−FOR	30.8	16.26	——	24.99	7.82	——	12.6	19.3	10.7	1.2	0.8
DAMA−15P−FOR	39.1	——	25.24	33.32	——	8.34	12.6	27.5	10.7	1.2	0.8
DAMA−15S−FOR	39.1	24.59	——	33.32	7.82	——	12.6	27.5	10.7	1.2	0.8
DBMA−25P−FOR	53.0	——	39.01	47.04	——	8.34	12.6	41.3	10.7	1.5	1.0
DBMA−25S−FOR	53.0	38.30	——	47.04	7.82	——	12.6	41.3	10.7	1.2	0.8
DCMA−37P−FOR	69.3	——	55.47	63.50	——	8.34	12.6	57.7	10.7	1.5	1.0
DCMA−37S−FOR	69.3	54.76	——	63.50	7.82	——	12.6	57.7	10.7	1.2	0.8
DDMA−50P−FOR	66.9	——	52.86	61.11	——	11.16	15.4	55.3	13.9	1.5	1.0
DDMA−50S−FOR	66.9	52.34	——	61.11	10.65	——	15.4	55.3	13.9	1.2	0.8




D※MA−＊P



D※MA−＊S



DETAIL RETAINING CLIP
(SCALE 10:1)



注1.図示の位置に "社名 "及び "品名略称 "を表示する。
2.本コネクタ用使用電線はAWG#20以下で絶縁外径がφ1.83以下.
3.インサート配列はSJ017083を参照のこと。

命名法

D※MA−＊※−FOR
- 特殊記号
- コンタクト無し
- コンタクト性別
- インサート配列
- シリーズ

4.パネル取付穴寸法はSJ013596を参照のこと。
5.コンタクトは添付されない為、別オーダーで所要数を要求のこと。（表−1参照）

表−1

適合電線 AWG No.	ピンコンタクト	ソケットコンタクト
#18又は2本の#22	330−5291−055	031−1007−054
#26,#28,#30	330−50264	031−50287
#20,#22,#24	330−5291−900	031−5130−000

△ 6.図示の位置にロット番号を表示する。

NOTE1.PRODUCTION CAMPANY LOGO "JAE" & PART NUMBER AS INDICATED.
2.APPLICABLE WIRE SIZE FOR THIS CONNECTOR IS BELOW AWG#20.
OUTER DIMENSION OF
3.FOR INSERT ARRANGEMENT, REFER TO DWG No. SJ017083.
4.FOR PCB CUTOUT DIMENSIONS, REFER TO DWG No. SJ013596.

DESIGNATION

D※MA−＊※−FOR
- MODIFY CODE
- NO CONTACTS
- CONTACT TYPE
- INSERT ARRANGEMENT
- SERIES

5.CONTACTS ARE NOT SUPPLIED WITH CONNECTORS.
PLEASE DEMAND NECESSARY NUMBER OF CONTACTS ON ANOTHER ORDER.
(SEE TABLE−1).

TABLE−1

APPLICABLE WIRE AWG No.	PIN	SKT
#18 OR 2#22	330−5291−055	031−1007−054
#26,#28,#30	330−50264	031−50287
#20,#22,#24	330−5291−900	031−5130−000

△ 6.LOT NUMBER AT THE LOCATION SHOWN IN THE DRAWING.

NO.	DESCRIPTION	QTY.	MATERIAL	FINISH	REMARKS
6	EXTRACTION TOOL	1	NYLON	——	
5	RETAINING CLIP	TABLE 2	COPPER ALLOY	——	
4	REAR INSULATOR	1	DIALLYLPHTHALATE	(COLOR:GREEN)	
3	FRONT INSULATOR	1	DIALLYLPHTHALATE	(COLOR:GREEN)	
2	REAR SHELL	1	STEEL	HEXAVALENT CHROMIUM FREE CHROMATE(TRIVALENT CHROMATE TREATMENT)ON ELECTROPLATED ZINC	
1	FRONT SHELL	1	STEEL	HEXAVALENT CHROMIUM FREE CHROMATE(TRIVALENT CHROMATE TREATMENT)ON ELECTROPLATED ZINC	

仕様書(SPECIFICATION) JACS−1045	第1版(ORIGINAL DATE) 31.Mar.2005	尺度(SCALE) 2:1	シリーズ(SERIES) Dsub
一般公差(GENERAL TOLERANCE) 寸法(DIMENSION): . ±0.8 / .X ±0.4 / .XX ±0.1 / .XXX± 角度(ANGLES): X° ± / XºX'±	製図 DR.	名称(TITLE) D※MA−＊※−FOR	日本航空電子工業株式会社 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.
	担当 CHK. Y.TAKAGI		
	査閲 APPD. ——		
	承認 APPD. Y.KUBOTA	質量(MASS)	図面番号(DRAWING NO.) SJ103088 / 版数(REV.) 2 / SIZE A2

JAE-CONNECTOR.COM Reference Only

DOF−0−213F(05.08)

0 10 20 30 40 50 60 70 80 90 100

JAE CONNECTOR DIV. PROPRIETARY.
COPYRIGHT (C) 2005, JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.