ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating: 3AMP

Temperature Range: −40℃to+105℃

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V


Material:


Insulator: Polyester (UL94V−0)


Standard: PA6T


Contact: Brass

Plating: Au over Ni









PCB LAYOUT

COSTOMER DRAWING				深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING				TITLE	排针PIN距2.54 塑高2.5 单排4PIN错位贴	REV.	A
CHECKED				PART NO.	LAIL-PZ2.54-4P-YT	UNITS	mm
APPROVED				DWG. NO.		Projection	
TOLERANCES ARE							
30-150	±0.35	ANGLE					
10-30	±0.2						
5-10	±0.15	±3°					
0-5	±0.1						