
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , .
© COPYRIGHT By – ALL RIGHTS RESERVED.


LOC	DIST
J	

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	REVISED ECR-14-010014	15NOV2014	I.T	W.H




SECT "B"–"B"



奇数極5,7極
ODD NUMBER Pos. 5,7 Pos.



4極 4Pos.
(SCALE 5:1)



偶数極6,8,10極
EVEN NUMBER Pos.6,8,10 Pos.
(SCALE 5–1)


注記
NOTES
1 嵌合相手製品型番及び、嵌合時寸法は
MATING COUNTER PART NUMBER AND DIMENSIONS
表–1 参照のこと。
AFTER MATING: SEE TABLE 1.


嵌合時寸法: 巾(mm)×高さ(mm)
DIMENSIONS AFTER MATING : WIDTH(mm) × HEIGHT(mm)

MATING COUNTER CONN 嵌合相手側コネクタ POST HDR ASSY			RECTN ASSY SMT V TYPE WITH BOSS X-174637-X
	製品型番 P/N	高さ H	
DIP TYPE	X-174642-X	3.95	4.4 (巾W) x 5.1 (高さH)
		5.95	4.4 (巾W) x 7.0 (高さH)
SMT TYPE	ボス無 WITHOUT BOSS X-174644-X ボス付 WITH BOSS X-174820-X	3.95	4.4 (巾W) x 5.1 (高さH)
		5.95	4.4 (巾W) x 7.1 (高さH)


TABLE 1 SMT TYPEは、巾及び高さ寸法に SMT TYPE INCLUDE DIMENSIONS
半田付タイン部寸法を含みます。 OF SOLDER DIP TINE.

△2 基板位置決め用ボス切断跡。
CUT MARK OF POSITIONER BOSS.
△3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
△4 OBSOLETE PARTS






20極 20Pos.
(SCALE 5–1)





SECT "A"–"A"



ボス形状 'A'
BOSS FORM 'A'








17極 17Pos.
(SCALE 5–1)

↑	25.45	23.75	26.45	20	△3 5– –0
'A'	21.70	20.00	22.70	17	△3 –7
'B'	12.95	11.25	13.95	10	4– –0
↑	10.45	8.75	11.45	8	3– –8
'A'	9.20	7.50	10.20	7	△4 3– –7
↑	7.95	6.25	8.95	6	△3 3– –6
	6.70	5.00	7.70	5	△4 3– –5
'B'	5.45	3.75	6.45	4	3–174637–4
ボス形状 BOSS FORM	C	B	A	極数 Pos.	型番 P/N

鉛フリー
LEAD FREE



P.C.B MOUNTING LAYUOUT
基板加工寸法
(適用基板厚 :0.6mm 最小)
(APPLICABLE P.C.B THK : 0.6mm MIN)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ± 1桁以下 : ±0.2
2 PLC ± 1桁超え 3桁以下 : ±0.25
3 PLC ± 3桁超え 10桁以下 : ±0.3
4 PLC ± 角度 : ±3°
ANGLES ±3°

MATERIAL: AS SHOWN 図中参照
FINISH: AS SHOWN 図中参照

DWN	S.KANEKI	13MAY91
CHK	J.TANIGAWA	13MAY91
APVD	S.KUBOUCHI	24DEC98
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT		

CUSTOMER DRAWING

TE Connectivity

NAME
1.25 F–P CONNECTOR (B–TO–B)
SINGLE ROW REC HDR ASS'Y (V) SMT TYPE
WITH BOSS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-174637	–

SCALE	SHEET	REV
10:1	1 OF 1	M