



Mechanical Dimensions: Inches [mm]

Tolerances ± 0.012 [0.3] Unless Otherwise Specified




Mounting Hole



Thickness	X	Y
0.03~0.05 [0.75~1.25]	0.75-0.004 [19.2-0.1]	0.51~0.004 [13.0+0.1]
0.05~0.1 [1.25-2.0]	0.76-0.004 [19.4-0.1]	0.51~0.004 [13.0+0.1]
0.1~0.12 [2.0~3.0]	0.78-0.004 [19.8-0.1]	0.51~0.004 [13.0+0.1]

Circuit Diagram

3P SPST OFF-ON (LED-D)



Electrical Specifications

Rating	16A 12V DC	
Contact Resistance	50m ohm Max	
Insulation Resistance	DC 500V 100M ohm Min	
Dielectric Strength	AC 1500V 1 minute	
Operation Temperature	-25°C~85°C	

Material Specifications

Frame	Black, Nylon 66
Actuator	Green, PC
LED	Green (Dependent)

Rocker Switch

RF1-1A-DC-2-GL



Rev Date of issue Revision Notes

Designed Approved

B	07-13-2021	Initial Drawing	RC	OF
---	------------	-----------------	----	----