
Part Number : 1731130173
Product Description : FCT High-Density D-Sub Connector, Male, Right-Angle, PCB Through Hole, Gold Plating, Grounding Bracket with Snap-in, 26 Circuits
Series Number : 173113
Status : Active
Product Category : D-Sub Connectors
Engineering Number : CT15-26P5-L228



Documents & Resources

Specifications
1731120006-PK-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173113
Description	FCT High-Density D-Sub Connector, Male, Right-Angle, PCB Through Hole, Gold Plating, Grounding Bracket with Snap-in, 26 Circuits
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	High Density
UPC	191128203043

Electrical

Current - Maximum per Contact	3.0A
Shielded	Yes

Physical

Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Durability (mating cycles max)	50
Gender	Male
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Steel
Net Weight	14.000/g
Number of Rows	3
Orientation	Right-Angle
Packaging Type	Tray
Panel Mount	Rear

Panel Mount Method	Thread-In
PC Tail Length	9.55mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.98mm
Pitch - Termination Interface	2.54mm
Plating - Contact	Gold over Nickel
Plating - Shell	Nickel
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +105°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT High-Density D-Sub, Size 2, 26 Position, Socket