



CAD FILE:

PIN ASSIGNMENT:



MATERIAL (IDC)
 INSULATOR: PBT (UL 94V-0)
 Contact: Copper Alloy.
 Contact Plated: Gold or Tin over Nickel Plated.

SPECIFICATIONS

TEMPERATURE RANGE: -20° C TO +105° C
 CONTACT RESISTANCE: 3Ω MAX
 INSULATION RESISTANCE: 5MΩ MIN.
 WITHSTANDING VOLTAGE: 300V 10S

Pin	A
6	2*3
8	2*4
10	2*5
12	2*6
14	2*7
16	2*8
18	2*9
20	2*10



序号	名称	规格说明	数量
1	端子	IDC-XXP 二件式 (2.54mm)	1
2	线材	2651/28#1.27间距灰排	1
3	卡扣	反扣-XXP (2.54mm)	1

APPROVALS		DATE		
DRAWN	G.M.Chen	2015/3/30		
CHECKED			TITLE:	LEADWIRE
APPROVALS			PART NO.	IDC-265126-200-XXP
TOLERANCES ARE		30~以上 ±0.30	ANGLE	UNIT: mm
		10~30 ±0.20		SCALE: 1:1
		5~10 ±0.15		SHEET 1 OF 1
		~ 5 ±0.10	±2'	DRAWING NO.
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
				CHECK.
				APPRO.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.