











www.xwxwdz.com

Technical requirements:

1、Unit: mm

2、Line diameter: 0.4

3、Material: carbon steel with nicked plated-meet ROHS

4、Style: horn mouth double pin

5、Technics: high temperature of the 260℃ heat treatment

6、No be marked sizes is ±0.25mm tolerances

7、No dirty surface,no bad material

8、Contact number: 13459252012、0592-5216722

9、Mode: F9-4.5-8-0.4-1.3UU

10、Salt spray test:

five precent salt spray test was met for 24hours

11、Packaging method: in bags-the mininum package is 1000pcs

						碳钢线		厦门市芯网电子科技有限公司
标记	处数	分区	更改文件号	签名	年 月 日	阶 段 标 记	重量	比例
设计						S		3:1
校核								
批准								