

REV.	DESCRIPTION	ECN NO.	NAME	DATE

备注(NOTE):

1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680, 镍底, 镀金0.5u)

1.3 外壳: 不锈钢304—表面镀镍50U

2 电气特性:

2.1 接触区: 接触电阻30mΩMax,

允许10mΩ变化量,

测试条件: 20mv, 100mA下测量,

2.2 额定电流: 最大3A

2.3 额定电压: 5V.

2.4 耐电电压: 100VAC.

2.5 绝缘电阻: 至少100兆欧

3 机械性能:






3.1 插入力: 0.5—2.0Kg

3.2 拔出力: 0.8—2.0Kg

3.3 插拔次数: 5000+.

4 工作环境: -20℃ — +85℃

4.1 盐雾测试: 24H



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x.° ±5.0° x.x° ±3.0° x.xx°	TITLE: TYPE-C 6P SMT 四脚		CHECKED: MAX
	DWG. NO.: UC17-0B06F68011		
	PART NO.: UC17-0B06F68011		APPROVED: WILL
	UNIT: mm	SCALE: none	
	DWG. SIZE: A4	LAYER: bxconn	

