330369 ✔ ACTIVE


SOLISTRAND

TE Internal #: 330369

Butt Splice, 12 – 10 AWG, 3 – 6 mm² Wire, Serrated, 5180 – 13100 CMA, Copper, 16 Serration, Length 14.4 mm [.567 in], Loose Piece, Closed Barrel

View on TE.com >

Terminals & Splices > Splices







Splice Type: **Butt Splice**

Wire Size: **3 – 6 mm²**

Sealable: **No**

Splice Features: **Serrated**

Features

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Contact Features

Terminal Plating Thickness	2.54 µm[100 µin]
Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Dimensions

Recovered Inside Diameter	3.28 mm[.129 in]
Outside Diameter	5.74 mm[.226 in]
Wire Size	5180 – 13100 CMA
Barrel Inside Diameter	3.28 mm[.129 in]
Terminal Material Thickness	1.07 mm[.042 in]
Product Length	14.4 mm[.567 in]

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	16
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Splice Features	Serrated

Mechanical Attachment

Wire Insulation Support	Without

Usage Conditions

Insulation Option	Uninsulated

Operation/Application

Compatible With Wire Base Material	Copper

Industry Standards

Government Qualified Splice	No

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 169400
CERTI-LOK FRAME W/O DIES




TE Part # 58546-1
PC 22-10 SOLISSPICE SPL I SHT

TE Part # 58545-4
SOLISTRAND 10-22 DIE ASSY.



TE Part # 49935
DAHT SOLIS 22-10 ASSY



TE Part # 47814
DIES SOLIS 12-10 DIE SET



TE Part # 58545-3
SDE DIE ASSY. 22-10 SOLISTRAND



TE Part # 58545-1
SOLISTRAND 10-22 DIE ASSY




TE Part # 525693
DAHT SOLIS 22-10 ASSY

Customers Also Bought



TE Part #1-66597-0
III+ PIN,18-14,30AU/FL,STRIP



TE Part #41495
SPADE .190(4.82 MM)12-10 AWG TPBR



TE Part #035377P003
ES1000-NO.3-B8-X-75MM



TE Part #829131P081
ES2000-NO.1-C1-0-100MM



TE Part #829131P012
ES2000-NO.1-C1-0-50MM




TE Part #063725P046
ES2000-NO.2-B9-0-100MM



TE Part #063725P031
ES2000-NO.2-B9-0-150MM



TE Part #121397P072
ES2000-NO.3-B8-0-100MM



TE Part #543633P070
SCT-NO.1-E6-0-305MM

TE Part #5-1437843-8
103092=7-1437843-9 BLACK

Documents

Product Drawings

SPLICE,SOLIS BUTT 12-10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_330369_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_330369_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_330369_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English